


TEC05-12

Power TEC Driver



Product features:

- output power up to 55 W
- efficiency up to 97 %
- ultra fast step response
- H-bridge for combined heat/cool operation
- USB- and RS485-interface
- operating with Pt1000 sensor



Product description:

The TEC05-12 is a very compact and powerful current source for Peltier elements. The device operates as a bidirectional regulated current source for the gentle operation of Peltier elements. We have deliberately avoided the use of pulse width modulation in order to keep the noise emission very low.

The device is therefore also suitable for tempering tasks in sensitive laboratory applications. The high efficiency makes additional cooling unnecessary in most cases. The robust base plate made of black anodized aluminum serves as a heat sink and allows a very easy installation for your application.

The TEC05-12 can be easily programmed and operated via the included "Config Utility" software. A plugin for LabVIEW is also available for free. The operation as a stand alone device is also very easy. The optionally available TEC display informs the user about interesting values such as temperature, current and operating status. The setpoint temperature can be conveniently set via pushbuttons and the TEC05-12 can be switched on and off.

Technical data:

Supply voltage	+12V
Supply current	max. 6A
Output voltage	-11 ... +11V
Output current	-5 ... +5A
Output current limit	cooling 0 ... -5A heating 0 ... +5A
Temp. range	-50°C ... 150°C
Temp. stability	up to 0.01°C
Temp. sensor ch1	Pt1000
Temp. sensor ch2	Pt1000
interfaces:	
ENABLE_IN	5V, TTL
TEMP_SET_IN	0 ... +4096mV
TEMP_OK_OUT	5V, TTL
FAN_PULSE_IN	5V, TTL, max 500Hz
FAN_PWM_OUT	5V, 25kHz
DISPLAY	for TECdisplay
operating temperature	-20 ... +85°C
Weight	85g
Dimensions	70x40x27mm

TECdisplay (optionally available)

